



Bedhead Units and Accessories



HOSPITAL BEDHEAD

BASIC

Ref.: 14CTbcdddd

The **BASIC Bedhead unit** is a wall bedhead that integrates the supply of medical gases, power, telephone and computer plugs, etc...

It can be mounted either in single, double or triple bars, effectively separating the electricity cables and the gas pipes. Our technical office will adjust the dimensions, colours and final equipment to the specific needs of each project upon demand.



TECHNICAL SPECIFICATIONS

Manufactured in:


- Structure and covers manufactured in *extruded aluminium*, forming removable compartments.
- Cover ends manufactured in *polystyrene*.

The dimensions are 74 mm depth by 120 mm canal.

Treatments:

- Main body lacquered: **RAL 9010**.
- Covers lacquered in:
 - Red: **RAL 3003**
 - Blue: **RAL 5015**
 - Green: **RAL 6019**
 - Grey: **RAL 7035**
 - White: **RAL 9010**

In compliance with **UNE-EN ISO 11197** standard.



C/ Tungsteno 11-15.
Arganda del Rey, 28500, Madrid
Telf.: +34 91 871 99 50
www.itcsal.com itcsal@itcsal.com



HOSPITALIZATION BEDHEAD

CLASSIC

Ref.: 14CHbcdddd

CLASSIC is a wall bedhead able to integrate the supply of medical gases, electrical, telephone and computer plugs and the call device for nursing assistance, as well as to cast indirect light to the patient's bed.

With basic components, our technical office will adapt the dimensions, colours and final equipment to the specific needs of each project upon demand.



TECHNICAL SPECIFICATIONS

Manufactured in:


- Structure and covers manufactured in *extruded aluminium*, forming independent recordable compartments.
- Translucent covers in *polycarbonate*.
- Cover ends in *ABS*.

Its dimensions are 117 mm depth by 238 mm height.

Finishing:

- Main body lacquered: **RAL 9010**.
- Covers lacquered in the following colours:
 - Red: **RAL 3003**
 - Blue: **RAL 5015**
 - Green: **RAL 6019**
 - Grey: **RAL 7035**
 - White: **RAL 9010**

In compliance with **UNE-EN ISO 11197** standard.



C/ Tungsteno 11-15.
Arganda del Rey, 28500, Madrid
Telf.: +34 91 871 99 50
www.itcsal.com itcsal@itcsal.com

09/2017-Rev.02



HOSPITALIZATION BEDHEAD

CLAIRE

Ref.: 14CCbcdddd

The **CLAIRE bedhead unit** is a hospital bedhead designed to respond to the highest aesthetics and functionality requirements, becoming another architectural element of the environment. The mechanisms, except the gas outlets, are incorporated to its lower profile, parallel to the ground, thus being hidden by the front cover.

Starting on some basic components, our technical office will adapt the dimensions, colours and final equipment to the specific needs of each project upon demand.



TECHNICAL SPECIFICATIONS

Manufactured in:


- Structure and covers manufactured in *extruded aluminium*, forming three independent and removable compartments.
- Translucent covers in *polycarbonate*.
- Covers ends in *ABS*.

Its dimensions are 122 mm depth and 233 mm height.

Finishings:

- Main body lacquered: **RAL 9010**.
- Covers lacquered in the following colours:
 - Red: **RAL 3003**
 - Blue: **RAL 5015**
 - Green: **RAL 6019**
 - Grey: **RAL 7035**
 - White: **RAL 9010**
- The front cover can be customized with different bedhead finishings for different services areas, and the image of the hospital can be incorporated.

In compliance with **UNE-EN ISO 11197** standard.



C/ Tungsteno 11-15.
Arganda del Rey, 28500, Madrid
Telf.: +34 91 871 99 50
www.itcsal.com itcsal@itcsal.com



HOSPITALIZATION BEDHEAD

VERTICAL CLAIRE

Ref.: 14CWbcdddd

The **Vertical CLAIRE bedhead** is a hospital bedhead designed to respond to the highest aesthetics and functionality requirements, becoming another architectural element of the environment. It is able to integrate the supply of medical gases, electrical, telephone and computer plugs and the call device for nursing assistance, as well as to cast indirect light to the patient's bed.

- There are several configurations for these bedheads: they have a standard structure that accommodates one or two Ø38 mm bars for the placement of trays, drawers, monitor or pump supports, etc... Our technical office will adapt the dimensions, colours and final equipment to the specific needs of each project on demand.



TECHNICAL SPECIFICATIONS

Manufactured in:

- Structure and covers in *extruded aluminium*, forming three independent compartments.
- Translucent covers in *polycarbonate*.
- Covers ends in *ABS*.
- Tubes in *stainless steel*.

Its dimensions are 122 mm depth and 233 mm width.

Finishing:

- Main body lacquered: **RAL 9010**.
- Covers lacquered in the following colours:
 - Red: **RAL 3003**
 - Blue: **RAL 5015**
 - Green: **RAL 6019**
 - Grey: **RAL 7035**
 - White: **RAL 9010**
- The front cover can be customized with different bedhead finishing for different services areas, and the image of the hospital can be incorporated.

In compliance with **UNE-EN ISO 11197** standard.

C/ Tungsteno 11-15.

Arganda del Rey, 28500, Madrid

Telf.: +34 91 871 99 50

www.itcsal.com

itcsal@itcsal.com



PENDANT BEDHEAD

NEXUS LT Pendant

Ref.: 14NTDcdefg / 14NTScdefg

The ceiling-pendant **NEXUS LT** columns are designed to integrate the supply of medical gases and electricity and communications plugs, and are specially indicated for surgical areas and intensive care and neonatal units.

- The column comprises a support to the ceiling and a horizontal profile containing six isolated compartments (three in the LT-S version), which can be equipped differently depending on the needs of each project.
- Its design displays the gas outlets in working arrangement, allowing the operator to connect flowmeters and vacuum regulators directly during delicate situations, avoiding connection by flexible pipes.
- Complemented with rotating racks of different heights, trays, drawers and diverse accessories from our rail commercial line



TECHNICAL SPECIFICATIONS

Manufactured in:

- Structure and covers in *extruded aluminium*, forming independent removable compartments.
- Translucent covers in *polycarbonate*.
- Covers ends in *polystyrene*.

Its dimensions are 414 mm depth by 255 mm height and 500 mm length.

Finishings:

- Main body lacquered: **RAL 9010**.
- Covers lacquered in the following colours:
 - Red: **RAL 3003**
 - Blue: **RAL 5015**
 - Green: **RAL 6019**
 - Grey: **RAL 7035**
 - White: **RAL 9010**

In compliance with **UNE-EN ISO 11197** standard.

C/ Tungsteno 11-15.
Arganda del Rey, 28500, Madrid
Tel.: +34 91 871 99 50
www.itcsal.com itcsal@itcsal.com



PENDANT BEDHEAD

NEXUS II LM / LX

Ref.: 14NM2cdefg / 14NX2cdefg

NEXUS II LM and **LX** pendant bedheads are designed to integrate the supply of medical gases and electricity and communications plugs, and are specially indicated for emergency wards, reanimation areas and intensive care units.

- **NEXUS II LM** bedhead has two brackets attached to the ceiling (three for the **LX** version) and a horizontal profile containing four isolated compartments, which can be equipped differently depending on the needs of each project.
- Complemented with only rotating or rotating and sliding racks of different heights, trays, drawers and diverse accessories from our rail commercial line.



TECHNICAL SPECIFICATIONS

Manufactured in:

- Structure and covers manufactured in *extruded aluminium*, forming independent removable compartments.
- Translucent covers in *polycarbonate*.
- Cover ends in *polystyrene*.

Its dimensions are 503 mm depth by 181 mm height and lengths of 3m for the LM version and 4,5m for the LX version, being able to install units of higher length by joining several bedheads.

Finishing:

- Main body lacquered: **RAL 9010**.
- Covers lacquered in the following colours:
 - Red: **RAL 3003**
 - Blue: **RAL 5015**
 - Green: **RAL 6019**
 - Grey: **RAL 7035**
 - White: **RAL 9010**

In compliance with **UNE-EN ISO 11197** standard.

C/ Tungsteno 11-15.
Arganda del Rey, 28500, Madrid
Telf.: +34 91 871 99 50
www.itcsal.com itcsal@itcsal.com

CE
0051

CSQ
MED
ISO 13485

CSQ
ISO 9001:2008




PENDANT BEDHEAD - Accessories

NEXUS Twistable cart / Twistable and sliding cart

Ref.: 14NTCcd00 / 14NCMcd000

This cart is capable of turning gently on a vertical axis and moving on the horizontal axis, holding equipment and accessories on the patient's bedhead, without the need of supports on the floor or on the walls.

- There are two standard lengths adaptable to each need. Both racks have four lateral profiles and two inferior ones for the anchoring of various accessories from our rail commercial line.
- Accessories such as shelves, drawers and auxiliary rails can be easily accommodated to vertical tubes with removable flanges, allowing a quick change in the configuration of the cart.



TECHNICAL SPECIFICATIONS

Manufactured in:

- Manufactured with *lacquered steel* profiles and $\varnothing 38$ mm *stainless steel* tubes.
- They have a frontal and an inferior system that enables displacement and turn blocking.
- Available in two widths and two standard heights, although the latter can be adapted to the client's needs.

Finishing:

- Lacquered: **RAL 9010**.
- Finishing elements available in the following colours:
 - Red: **RAL 3003**
 - Blue: **RAL 5015**
 - Green: **RAL 6019**
 - Grey: **RAL 7035**

Maximum load: 150 kg.

C/ Tungsteno 11-15.
Arganda del Rey, 28500, Madrid
Telf.: +34 91 871 99 50
www.itcsal.com itcsal@itcsal.com




OTHER ACCESSORIES

Telescopic arm and swivelling dividers

Ref.: 13SPTL0000 / 14SPTL0000

Dividing curtain specially designed to preserve privacy between patients, being able to monitor them by a standing up person.

- The support is extended by pulling the control located on one of the edges and is gathered again by pushing in the opposite direction, being possible also to arrange it in parallel to the wall to clear room when it is not in use.
- Rail version, wall version and $\varnothing 38,0$ mm tube version available.



TECHNICAL SPECIFICATIONS

- Manufactured in *anodized aluminium, chromium-plated brass and stainless steel.*
- Length gathered / extended: 590 / 1510 mm.
- Curtain area: 1500 x 1000 mm.
- Delivered in a package of 5 disposable curtains.

C/ Tungsteno 11-15.
Arganda del Rey, 28500, Madrid
Telf.: +34 91 871 99 50
www.itcsal.com itcsal@itcsal.com

09/2017-Rev.02



MONITOR SUPPORTS

Adjustable monitor stand

Ref.: 13SPOR8000 / 14SPOR8000

Specially designed to support bedhead monitors, allowing its orientation on a vertical axis and its inclination by means of a lower control, it enables visualization from any point.

- The rail version is attached by means of a clamp with two knobs, while the wall version is attached thanks to a slide vertical profile. The Ø38 mm version is fixed by two flanges.
- Every model has a practical basket coated in white.
- The standard version includes a stand with buckles. In addition there are specific versions adjusted to *General Electric*, *PHILIPS SureSigns* and *MP* monitors, as well as some other brands on the market.



TECHNICAL SPECIFICATIONS

Manufactured in *anodized aluminium* (profiles) and *zinc steel*.

- The standard platform is 300 mm wide by 180 mm deep. It includes a buckle to secure the monitor.
- The horizontal arm is 220 mm long and has an inferior reinforcement.
- The vertical profile is 500 mm long and allows an adjustment of 270 mm within the total height of the set, thanks to its rails.
- **Rotations:**
 - Lateral rotation: 150°.
 - Tilt from 0° to 15°.
- **Weight:**
 - Rail version: 2,7 kgr.
 - Wall version: 3,3 kgr.
 - Ø38mm tube version: ????
- **Maximum load:** 25 kg.

C/ Tungsteno 11-15.
Arganda del Rey, 28500, Madrid
Telf.: +34 91 871 99 50
www.itcsal.com itcsal@itcsal.com

09/2017-Rev.02




PENDANT CARTS - Accessories

Metallic drawer

Ref.: aaCJbcdefg

Set of drawers attached to different cart and bedhead structures.

- It is composed by an upper shelf, drawers in different formats and side flanges that allow its installation on the cart structure and its subsequent regulation.
- The inner drawer buckets can be easily extracted out of the drawers for their cleaning or manipulation.
- Thanks to the slide partitions, it is possible to establish different divisions in the interior of the drawers.



TECHNICAL SPECIFICATIONS

Manufactured in:

- Upper shelf manufactured with a *lacquered steel sheet (RAL 9010)*.
- Drawers manufactured in *ABS* and available in 400 x 300 mm and in 600 x 400 mm dimensions with 50, 100 and 200 mm in height.
- The interior dividers are manufactured in *ABS*.
- The exterior structure is made of *lacquered extruded aluminium in white (RAL 9010)*.
- Finishing elements in *ABS* with different colours.

Finishing:

- Lacquered: **RAL 9010**.
- Finishing elements in the following colours:
 - Red: **RAL 3003**
 - Blue: **RAL 5015**
 - Green: **RAL 6019**
 - Grey: **RAL 7035**

C/ Tungsteno 11-15.
Arganda del Rey, 28500, Madrid
Telf.: +34 91 871 99 50
www.itcsal.com itcsal@itcsal.com

09/2017-Rev.02



PENDANTS CARTS - Accessories

Metallic Shelf

Ref.: aaBbcd0000

Shelves attached to different cart and bedhead structures.

- Designed with a small projection along the perimeter to prevent objects from falling.
- They have two side flanges in order to adapt to the cart structures, enabling a quick regulation.



TECHNICAL SPECIFICATIONS

Manufactured in:

- Shelf manufactured with a *lacquered steel sheet (RAL 9010)*.
- The finishing elements are made of *ABS* in different RAL colours.

Finishings:

- Lacquered: **RAL 9010**.
- Finishing elements available in the following colours:
 - Red: **RAL 3003**
 - Blue: **RAL 5015**
 - Green: **RAL 6019**
 - Grey: **RAL 7035**

Maximum load: 25 kgr.

C/ Tungsteno 11-15.
Arganda del Rey, 28500, Madrid
Telf.: +34 91 871 99 50
www.itcsal.com itcsal@itcsal.com

09/2017-Rev.02




LAMPS

Recognition LED lamp to rail

Ref.: 13LAMP6000

The newest recognition lamp is the lamp of cold light, which relies on LED diodes technology. It is indicated for any medical specialty, but mainly for those places where a total absence of calorific radiation is required and a very good light quality is still needed. Note the long life of the LED diodes, almost unlimited, and its low energetic consumption, lower than 10 W.

Its design and robustness make it fit for every kind of use in clinics, hospitals and consultation facilities. Rail version and Ø38mm tube version available, thus being able to adapt to any work area. High mobility thanks to the high quality and reliability of the flex tube. Together with the lozenge next to the cupola, they make this device able to adapt to an infinity of positions.



TECHNICAL SPECIFICATIONS

- Voltage: 95-240V, 50-60 Hz.
- Light source: LED.
- Luminous angle: 6°.
- Power: 10 W
- Short circuit protection: Yes.
- Thermal protection: Yes.
- Lifetime: 50.000 hours.
- Luminous intensity: 42 Klux / 0,5 m; 12Klux / 1,0 m
- Colour temperature: 4.750 K
- Light field diameter to 1m: 12 cm

C/ Tungsteno 11-15.
Arganda del Rey, 28500, Madrid
Telf.: +34 91 871 99 50
www.itcsal.com itcsal@itcsal.com



SUPPORT FOR DROPPERS AND INFUSION PUMPS


Support for droppers to rail



Ref.: 13G2RL0000 / 13GTRLDC00 / 13G4RL0000

Hangers of different types for serum bags to prevent obstacles on the floor.

- The mount incorporates a clamp with a knob, which anchors the hanger firmly to the rail. In addition, a knob allows vertical repositioning for an easier access to the hooks.



TECHNICAL SPECIFICATIONS

- Manufactured in *anodized aluminium*.
- Bars of either $\varnothing 13 \times 450 \times 850$ mm (with two folds) or $\varnothing 13 \times 450 \times 1000$ mm (in right angle) dimensions.

C/ Tungsteno 11-15.
Arganda del Rey, 28500, Madrid
Telf.: +34 91 871 99 50
www.itcsal.com itcsal@itcsal.com

09/2017-Rev.02




SUPPORT FOR DROPPERS AND INFUSION PUMPS

Infusion pumps holder



Ref.: 13SPBM0000 / 13SCCG3500

Holder specially designed to anchor infusion pumps at the bedhead of the patient.



TECHNICAL SPECIFICATIONS

Infusion pump holders for rail (ref.: 13SPBM0000):

- Manufactured in *anodized aluminium* of $\varnothing 25 \times 1180$ mm dimensions with a telescopic extension for four bags of serum.
- Anchored to two rails by means of pushbutton clamps.

Infusion pumps holders for rail (ref.: 13SCCG3500):

- Manufactured in *anodized aluminium* of $\varnothing 25 \times 350$ mm dimensions with a telescopic extension for two bags of serum.
- Anchored to a rail by means of a clamp with knob.

C/ Tungsteno 11-15.
Arganda del Rey, 28500, Madrid
Telf.: +34 91 871 99 50
www.itcsal.com itcsal@itcsal.com

09/2017-Rev.02



OTHER ACCESSORIES

Basket

Ref.: 13CI251815

Practical attachable basket coated in white, able to contain sleeves for blood pressure devices or any other accessory of similar dimensions and weight.

- Rail version with a pushbutton clamp and a Ø38 mm tube version with a flange.



TECHNICAL SPECIFICATIONS

Manufactured with *stainless steel* wire.

Dimensions: 250 x 180 x 150 mm

C/ Tungsteno 11-15.
Arganda del Rey, 28500, Madrid
Telf.: +34 91 871 99 50
www.itcsal.com itcsal@itcsal.com

09/2017-Rev.02




OTHER ACCESSORIES

Glove container and sample tubes holder for rail

Ref.: 13ACCS2C00

Its top part has different holes to harbor sample tubes, while the lower space is destined to disposable gloves.

- Attached to the rail with a pushbutton clamp.



TECHNICAL SPECIFICATIONS

Manufactured in *stainless steel*.

C/ Tungsteno 11-15.
Arganda del Rey, 28500, Madrid
Telf.: +34 91 871 99 50
www.itcsal.com itcsal@itcsal.com

09/2017-Rev.02



OTHER ACCESSORIES

Waste collector holder for rail

Ref.: 13ACCS4A00

Metallic ring with exterior elastic to hold garbage bags, preventing them from resting on the floor.



TECHNICAL SPECIFICATIONS

Manufactured in *lacquered aluminium* in white (**RAL 9010**) with *silicone* elastics.
Dimensions: 300 x 200 mm.

C/ Tungsteno 11-15.
Arganda del Rey, 28500, Madrid
Telf.: +34 91 871 99 50
www.itcsal.com itcsal@itcsal.com

09/2017-Rev.02



JUST FLOW F - Series

Ball flowmeters

Ref.: See table

JUST FLOW F Series flowmeters can be used in medical facilities with an available gas piped network.

- Available for oxygen and medical air (*consult our staff for other gases*).
- Scales of 4, 6 or 15 l/min, twistable 360° to facilitate its reading.
- Available with a humidifier bottle, selector-bearing direct outlet. By turning a small side handle or a revolver system, the selector diverts the flow of the humidifier to a tube spigot.
- It can be provided individually or on a dual version, and it can be mounted either with a direct connector, a clamp to a rail or a $\varnothing 38$ mm bar flange. It is fed by a flexible hose with different European and American connectors (see *Connectors and Outlets*).



Just Flow
F-SERIES



TECHNICAL SPECIFICATIONS

- Manufactured in *anodized aluminium, polycarbonate, polyamide and chromed-plated brass*.
- **Outlet connection:** DISS 9/16".
- **Supply:** 4,5 bar.
- **Calibration:** 101,3 kPa and 23°C.
- **Precision:** ± 10 %.
- **Dimensions:**
 - Simple model: $\varnothing 31 \times 140$ mm
 - Double output handle selector: $\varnothing 35 \times 151$ mm.
 - Double output revolver selector: $\varnothing 31 \times 160$ mm
- **Weight:**
 - Simple model: 130 gr.
 - Double output handle selector: 180 g.
 - Double output revolver selector: 215 g.
- In compliance with **UNE-EN ISO 15002** standard.

C/ Tungsteno 11-15.
Arganda del Rey, 28500, Madrid
Telf.: +34 91 871 99 50
www.itcsal.com itcsal@itcsal.com

09/2017-Rev.02



JUST FLOW F - Series

Ball flowmeters



Ref.: See table

References for flow range 0 to 15 l/min

Standards	DIN 13260	NF S 90-116	BS 5682
Type			
JUST FLOW F + Connector	11FLSXDN15	11FLSXNF15	11FLSXBS15
JUST FLOW F Double output + Connector	11FLUXDN15	11FLUXNF15	11FLUXBS15
JUST FLOW F Double mounting	11FRSXDN15	11FRSXNF15	11FRSXBS15
JUST FLOW F Double mounting - Double output	11FRUXDN15	11FRUXNF15	11FRUXBS15
JUST FLOW F Rail - Knob clamp	13FPSXDN15	13FPSXNF15	13FPSXBS15
JUST FLOW F Rail - Pushbutton clamp	13FLSXDN15	13FLSXNF15	13FLSXBS15
JUST FLOW F Rail - Double output - Knob clamp	13FPUXDN15	13FPUXNF15	13FPUXBS15
JUST FLOW F Rail - Double output - Pushbutton clamp	13FLUXDN15	13FLUXNF15	13FLUXBS15
JUST FLOW F Rail - Double mounting - Knob clamp	13FTSXDN15	13FTSXNF15	13FTSXBS15
JUST FLOW F Rail - Double mounting - Pushbutton clamp	13FSSXDN15	13FSSXNF15	13FSSXBS15
JUST FLOW F Rail - Double mounting - Double output - Knob clamp	13FTUXDN15	13FTUXNF15	13FTUXBS15
JUST FLOW F Rail - Double mounting - Double output - Pushbutton clamp	13FSUXDN15	13FSUXNF15	13FSUXBS15
JUST FLOW F with Ø38 flange + Connector	14FLSXDN15	14FLSXNF15	14FLSXBS15
JUST FLOW F with Ø38 flange Double output + Connector	14FLUXDN15	14FLUXNF15	14FLUXBS15
JUST FLOW F with Ø38 flange Double mounting	14FRSXDN15	14FRSXNF15	14FRSXBS15
JUST FLOW F with Ø38 flange Double mounting - Double output	14FRUXDN15	14FRUXNF15	14FRUXBS15

¹ Medical Air models, replace X with M (please consult our staff about other gases).

² For other flow rates, replace 15 with 04 or 06, depending on flow rates of 4 l/min or 6 l/min (please consult our staff about other flow rates).

³ Please consult our staff about other gas standards.

⁴ Please consult our staff about other models.

C/ Tungsteno 11-15.

Arganda del Rey, 28500, Madrid

Telf.: +34 91 871 99 50

www.itcsal.com

itcsal@itcsal.com

09/2017-Rev.02



JUST FLOW C - Series

Dial flowmeters

Ref.: See table

JUST FLOW C Series flowmeters can be used in medical facilities with an available gas piped network.

- Turning the top control button the operator can select the flow that will be supplied by its inferior connection. This selection appears in the front display. Models available for oxygen and medical air with **4, 8, 15, 25 or 50 l/min** top range.
- Models available with a direct outlet to a humidifier bottle and with a flow selector which, turning a little front handle, diverts the humidifier flow towards a front nozzle for flexible hoses.
- It can be provided individually or on a dual version, and it can be mounted either with a direct connector, a clamp to a rail or a $\varnothing 38\text{mm}$ bar flange. It is supplied by a flexible hose with different European and American connectors (see *Connectors and Outlets*).



Just Flow
C-SERIES



TECHNICAL SPECIFICATIONS

- Manufactured in *anodized aluminium, ABS, stainless steel and chromed-plated brass.*
- In the version including a flow selector, the outlet connection is DISS 9/16"-type with a side nozzle for flexible hoses.
- **Supply:** 4,5 \pm 0,5 bar.
- **Calibration:** 101,3 kPa and 23°C.
- **Precision:** Q \leq 1,5 l/min \rightarrow \pm 30 %; Q > 1,5 l/min \rightarrow \pm 20%;
- **Dimensions:**
 - Simple model: $\varnothing 40 \times 56$ mm
 - Double output model: $\varnothing 40 \times 76$ mm.
- **Weight:**
 - Simple model: 85 gr.
 - Double output model: 140 gr.
- In compliance with **UNE-EN ISO 15002** standard.

C/ Tungsteno 11-15.
Arganda del Rey, 28500, Madrid
Telf.: +34 91 871 99 50
www.itcsal.com itcsal@itcsal.com

01/2019-Rev.03

CE
0051

CSQ
MED
ISO 13485

CSQ
ISO 9001:2008



JUST FLOW C - Series

Dial flowmeters



Ref.: See table

References for flow range from 0 to 15 l/min

Type	Standards		
	DIN 13260	NF S 90-116	BS 5682
JUST FLOW C + Connector	11CLSXD15	11CLSXNF15	11CLSXBS15
JUST FLOW C with selector + Connector	11CLUXD15	11CLUXNF15	11CLUXBS15
JUST FLOW C Double mounting	11CRSXDN15	11CRSXNF15	11CRSXBS15
JUST FLOW C Double mounting - with selector	11CRUXDN15	11CRUXNF15	11CRUXBS15
JUST FLOW C Rail - Knob clamp	13CPSXD15	13CPSXNF15	13CPSXBS15
JUST FLOW C Rail - Pushbutton clamp	13CLSXD15	13CLSXNF15	13CLSXBS15
JUST FLOW C Rail - With selector - Knob clamp	13CPUXDN15	13CPUXNF15	13CPUXBS15
JUST FLOW C Rail - With selector - Pushbutton clamp	13CLUXD15	13CLUXNF15	13CLUXBS15
JUST FLOW C Rail - Double mounting - Knob clamp	13CTSXD15	13CTSXNF15	13CTSXBS15
JUST FLOW C Rail - Double mounting - Pushbutton clamp	13CSSXD15	13CSSXNF15	13CSSXBS15
JUST FLOW C Rail - Double mounting - With selector - Knob clamp	13CTUXDN15	13CTUXNF15	13CTUXBS15
JUST FLOW C Rail - Double mounting - With selector - Pushbutton clamp	13CSUXDN15	13CSUXNF15	13CSUXBS15
JUST FLOW C with Ø38 tube flange + Connector	14CLSXD15	14CLSXNF15	14CLSXBS15
JUST FLOW C with selector with Ø38 tube flange + Connector	14CLUXD15	14CLUXNF15	14CLUXBS15
JUST FLOW C Double mounting with Ø38 tube flange	14CRSXDN15	14CRSXNF15	14CRSXBS15
JUST FLOW C Double mounting with Ø38 tube flange - with selector	14CRUXDN15	14CRUXNF15	14CRUXBS15

¹ Medical Air models, replace X with M (please consult our staff about other gases).

² For other top of range replace 15 with 04, 08, 30 or 50, depending on flow rates of 4 l/min, 8 l/min, 30 l/min or 50 l/min (please consult our staff about other flow rates).

³ Please consult our staff about other gas standards.

⁴ Please consult our staff about other models.

Available flows:

Modelo/Model/Modèle	Available flows / Caudales / Débits disponibles (L/min)	Precisión / Precision /Précision
0 - 4	0 - 0,2 - 0,4 - 0,6 - 0,8 - 1 - 1,5 - 2 - 2,5 - 3 - 3,5 - 4	Q ≤ 1,5 l/min → ±30% Q > 1,5l/min → ±20%
0 - 8	0 - 0,3 - 0,6 - 1 - 1,5 - 2 - 3 - 4 - 5 - 6 - 7 - 8	
0 - 15	0 - 0,5 - 1 - 2 - 3 - 4 - 5 - 6 - 8 - 10 - 12 - 15	
0 - 30	0 - 1 - 2 - 4 - 6 - 8 - 10 - 12 - 15 - 20 - 25 - 30	
0 - 50	0 - 3 - 6 - 10 - 15 - 20 - 25 - 30 - 35 - 40 - 45 - 50	

C/ Tungsteno 11-15.
 Arganda del Rey, 28500, Madrid
 Telf.: +34 91 871 99 50
www.itcsal.com itcsal@itcsal.com



JUST VAC Series

Vacuum regulators HV

Ref.: See table

The high vacuum regulator **JUST VAC** provides regulation of continuous suction for its use in tracheal and pharyngeal ways during surgical procedures and continuous gastric drainage.

- The vacuum regulator provides suction from 0 to total suction.
- They are classified as *High Vacuum / High Flow*.
- For the safety of the patient, in case of accidental connection to a positive gas pressure, the regulators can be equipped with an optional positive pressure relief valve.
- **JUST VAC** incorporates an ON-OFF dispositive, through which the aspiration can be switched off without having to close the suction control valve.
- It can be provided individually or on a dual version, and it can be mounted either with a direct connector, a clamp to a rail or a $\varnothing 38$ mm bar flange. It is supplied by a flexible hose with different European and American connectors (see *Connectors and Outlets*).
- Pressing the **PUSH** button, the accessories like filters, filters with overflow trap, DISS connectors or metallic connectors for flexible hoses are released for its easy replacement, ensuring the safety of the user and the patient (please see the *PUSH Accessories catalogue*).
- The original set includes the regulator, a disposable filter with safety overflow trap, three disposable filters and a metallic connector for flexible hose.



JustVac



TECHNICAL SPECIFICATION

- Manufactured in ABS (white/black for HV and yellow/black for LV), stainless steel, brass and NBR.
- Modes: ON, OFF.
- Ranges:
 - High vacuum: 0-760 mmHg.
- Supply: from 400 to 500 kPa.
- Vacuum gauge's precision: $\pm 2,5$ % FS.
- Inlet connection: 1/4" BSP in stainless steel.
- PUSH System for a quick and easy replacement of accessories.
- Dimensions: 158 x 89 x 63 mm
- Weight: 307 gr (without connection).
- In compliance with UNE-EN ISO 10079-3 standard.

C/ Tungsteno 11-15.
Arganda del Rey, 28500, Madrid
Telf.: +34 91 871 99 50
www.itcsal.com itcsal@itcsal.com

CE
0051

CSQ
MED
ISO 13485

CSQ
ISO 9001:2008



JUST VAC Series

Vacuum regulators HV



Ref.: See table

References

Type	Standards		
	DIN 13260	NF S 90-116	BS 5682
JUST VAC HV + Connector	11VPAVAEDN	11VPAVAENF	11VPAVAEBS
JUST VAC HV double mounting + Connector	11VPAAREDN	11VPAARENF	11VPAAREBS
JUST VAC HV to rail - Knob clamp	13VPAVAEPD	13VPAVAEPN	13VPAVAEPB
JUST VAC HV to rail double mounting - Knob clamp	13VPAAREPD	13VPAAREPN	13VPAAREPB
JUST VAC HV with Ø38,0 tube flange	14VPAVAEPD	14VPAVAEPN	14VPAVAEPB
JUST VAC HV with Ø38,0 tube flange double mounting	14VPAAREPD	14VPAAREPN	14VPAAREPB

¹ Other outputs replace E (disposable filter) with: D (DISS output), T (filter with safety overflow trap), F (bottle of 0,5 l), M (Metallic nipple) or O (free output).

² Other rail mounting replace P (knob clamp) with: G (pushbutton clamp), R (wall plate) or H (bearing plate)

³ For other gases please consult the standards.

⁴ Consult our staff for other models.

C/ Tungsteno 11-15.
Arganda del Rey, 28500, Madrid
Telf.: +34 91 871 99 50
www.itcsal.com itcsal@itcsal.com

